

# TOTALCEM

Self-etching and self-adhesive  
permanent resin cement  
Special for metal  
DEFINITIVE CEMENTATION

ویزگی ها

همه با هم در یک محصول: اچینگ + باندینگ + سمان (All in one)

قدرت باندینگ استثنایی

کیور دوگاهه (لایت و سلف کیور)

کیور شدن تضمین شده در نواحی پا دسترسی و نفوذ نور کم

ژل حالت پهیته شده برای برداشته شدن راحت اضافات (۳ تا ۴ ثانیه کیور کنید)

بدون ایجاد حساسیت بعد از درمان

لایه نازک حدود ۱ میکرون



غیر قابل حل در مایعات داخل دهانی

سیلینگ عالی

قابل استفاده بر روی دندان طبیعی

ماندگاری رنگ طولانی مدت

جهت نگهداری بهتر، محصول درون یخچال نگه داری شود



## موارد مصرف

برای inlay onlay کراون، پریج، پست Cementation  
بر روی مینا، عاج و فلز: Self-adhesive on

## Technical data

Compressive strength:	180 MPa
Water sorption:	12 µg/mm <sup>3</sup>
Solubility:	7 µg/mm <sup>3</sup>
Film thickness:	10 µm
Radiopacity, % Aluminium:	250
Fluor release (cumulative on 14 days):	589 ppm
Working time:	1.5 to 3.5 min
Setting time:	2.5 to 4.5 min
Compatible with all lamps:	Yes

## References

### TotalCem translucent

Syringe of 8g + 10 mixing tips + 10 fine intra-oral tips  
+ 10 extra-fine intra-oral tips ..... TTLCEM-TR

### TotalCem A2 universal

Syringe of 8g + 10 mixing tips + 10 fine intra-oral tips  
+ 10 extra-fine intra-oral tips ..... TTLCEM-A2

### TotalCem TR - Value Pack

3 Translucent syringes of 8g + 30 mixing tips + 30 fine intra-oral tips  
+ 30 extra-fine intra-oral tips ..... TCEM3-VPTR

### TotalCem A2 - Value Pack

3 A2 syringes of 8g 30 mixing tips + 30 fine intra-oral tips + 30 extra-fine intra-oral tips ..... TCEM3-VPA2

### Tips

25 mixing tips + 25 fine intra-oral tips ..... DCE-50

### Extra-Fine Tips

25 mixing tips + 25 extra-fine intra-oral tips ..... DCEXXF-50

### Ultra-Fine Colibri Tips

10 flexible and ultra-fine tips ..... DCCOL-10